


Air Cooler Performance in a 25 °C Ambient Environment



How to use the Performance Graph:

1. Select Performance Line.

The diagonal lines shown represent cooling performance at the indicated ambient air temperature. Performance lines at other ambient temperatures can be seen on the data sheet for each specific cooler.

2. Select Desired Temperature.


Draw a horizontal line on the graph corresponding to your desired enclosure temperature until it intersects with the performance line corresponding to the ambient temperature at which the cooler is to operate.

NOTE: heating performance is not shown. Contact TE Technology, Inc. if you require this information.

3. Determine Cooling Capacity.

The maximum amount of heat that the cooler can remove is determined by the intersection point (determined in the previous step).

If the heat load exceeds the cooling capacity, then the cooler will not be able to maintain the desired temperature. If the heat load is less, then the cooler can operate with less input power.


TE TECHNOLOGY, INC. Expert Engineering, Precision Manufacturing
Quality Thermal Solutions Delivered


www.tetech.com • cool@tetech.com • 231-929-3966 • 1590 Keane Drive • Traverse City, MI 49696

Cold Plate Coolers	Heat Pumping (Watts), $\Delta T=0^\circ\text{C}$, 35°C Ambient		Heat Pumping (Watts), $\Delta T=0^\circ\text{C}$, 25°C Ambient		Operating Voltage (Volts)		Operating Current (Amps), Typical		Hot-side Fan Current (Amps), Maximum		Overall Dimensions (mm) length X width X height		Can be Customized with Large Orders		Can be Used for Cooling and Heating		Weight (Kg)		Heat Sink Airflow Parallel and Heating *		External Fan Noise (dBA)		TC-24-10		TC-36-25 RS485		TC-48-20 RS232 Series		TC-48-20 OEM		TC-720 OEM		TC-720		PS-12-8.4A		PS-24-6.5		PS-24-12.5		PS-24-25	
	CP-031	30	28	12	4.5	5.5	0.24	102 X 80 X 91	•	•	0.9	V	35	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•			
CP-031HT	30	28	12	4.5	5.5	0.24	102 X 80 X 91	•	•	0.9	V	35	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				
CP-036	33	32	12	4.7	5.7	0.58	152 X 127 X 114	•	•	1.8	V	44	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•			
CP-036HT	32	31	12	4.7	5.7	0.58	152 X 127 X 114	•	•	1.8	V	44	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•			
CP-040HT	41	40	24	2.7	3.3	0.24	140 X 67 X 89	•	•	0.8	V	47	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•			
CP-061	65	62	24	4.6	5.7	0.23	198 X 194 X 127	•	•	2.3	P	39	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
CP-061HT	59	56	24	4.5	5.4	0.23	198 X 194 X 127	•	•	2.3	P	39	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•			
CP-065	60	57	24	4.5	5.5	0.34	178 X 127 X 114	•	•	2.2	V	44	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
CP-110	105	101	24	9.0	10.9	0.50	203 X 130 X 140	•	•	3.0	V	47	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
CP-121	128	123	24	9.2	11.1	0.46	198 X 188 X 119	•	•	4.2	P	42	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
CP-200	206	198	24	14.1	17.3	1.00	254 X 176 X 165	•	•	6.3	V	55	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
CP-200HT	204	196	24	14.1	17.4	1.00	254 X 176 X 165	•	•	6.3	V	55	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
CP-200HTTT	204	196	24	14.1	17.4	1.00	254 X 176 X 206	•	•	6.7	V	55	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
CP-200TT	206	198	24	14.1	17.3	1.00	254 X 176 X 206	•	•	6.7	V	55	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
Specifications													Temperature Controllers						Power Supplies																							

CE Marked
RoHS Compliant


*Requires bipolar (heat/cool) controller.

Visit <https://tetech.com/product-category/cold-plate-coolers/> to view our cold plate cooler products & data sheets.

TE TECHNOLOGY, INC.  Expert Engineering, Precision Manufacturing
Quality Thermal Solutions Delivered

www.tetech.com • cool@tetech.com • 231-929-3966 • 1590 Keane Drive • Traverse City, MI 49696

Cold Plate Cooler Performance in a 25 °C Ambient Environment



How to use the Performance Graph:

1. Select Performance Line.

The diagonal lines shown represent cooling performance at the indicated ambient air temperature. Performance lines at other ambient temperatures can be seen on the data sheet for each specific cooler.

2. Select Desired Temperature.

Draw a horizontal line on the graph corresponding to your desired enclosure temperature until it intersects with the performance line corresponding to the ambient temperature at which the cooler is to operate.

NOTE: heating performance is not shown. Contact TE Technology, Inc. if you require this information.

3. Determine Cooling Capacity.

The maximum amount of heat that the cooler can remove is determined by the intersection point (determined in the previous step).

If the heat load exceeds the cooling capacity, then the cooler will not be able to maintain the desired temperature. If the heat load is less, then the cooler can operate with less input power.

TE TECHNOLOGY, INC. [®] Expert Engineering, Precision Manufacturing
Quality Thermal Solutions Delivered

www.tetech.com • cool@tetech.com • 231-929-3966 • 1590 Keane Drive • Traverse City, MI 49696

Liquid Coolers

Heat Pumping (Watts), $\Delta T=0^\circ\text{C}$,
35 °C Inlet Water Temperature

Heat Pumping (Watts), $\Delta T=0^\circ\text{C}$,
25 °C Inlet Water Temperature

Operating Voltage (Volts)

Operating Current (Amps), Typical

Hot-side Fan Current (Amps), Maximum

Overall Dimensions (mm), length X width X height

Can be Customized with Large Orders

Can be Used for Cooling and Heating

Weight (Kg)

Heat Sink Airflow Parallel/Vertical *

External Fan Noise (dBA)

TC-24-10

TC-36-25 RS485

TC-36-25 RS232-Series

TC-48-20 OEM

TC-48-20

TC-720 OEM

TC-720

PS-12-8.4A

PS-24-6.5


PS-24-12.5

	Heat Pumping (Watts), $\Delta T=0^\circ\text{C}$, 35 °C Inlet Water Temperature	Heat Pumping (Watts), $\Delta T=0^\circ\text{C}$, 25 °C Inlet Water Temperature	Operating Voltage (Volts)	Operating Current (Amps), Typical	Hot-side Fan Current (Amps), Maximum	Overall Dimensions (mm), length X width X height	Can be Customized with Large Orders	Can be Used for Cooling and Heating	Weight (Kg)	Heat Sink Airflow Parallel/Vertical *	External Fan Noise (dBA)	TC-24-10	TC-36-25 RS485	TC-36-25 RS232-Series	TC-48-20 OEM	TC-48-20	TC-720 OEM	TC-720	PS-12-8.4A	PS-24-6.5	PS-24-12.5	
LC-061	56	54	24	4.5	5.5	0.34	178 X 127 X 97	•	•	2.0	V	44	•	•	•	•	•	•	•	•	•	•
LC-200	192	185	24	14.1	17.3	1.00	254 X 176 X 155	•	•	5.8	V	55	•	•	•	•	•	•	•	•	•	•
CP-061 + SSX1	62	58	24	4.6	4.7	0.23	198 X 194 X 139	•	•	2.7	P	39	•	•	•	•	•	•	•	•	•	•
CP-065 + SSX1	57	53	24	4.5	5.5	0.34	178 X 127 X 127	•	•	2.7	V	44	•	•	•	•	•	•	•	•	•	•
CP-110 + SSX1	99	104	24	9.0	10.9	0.50	203 X 130 X 153	•	•	3.4	V	47	•	•	•	•	•	•	•	•	•	•
CP-121 + SSX1	118	113	24	9.2	11.1	0.46	198 X 188 X 136	•	•	4.6	P	42	•	•	•	•	•	•	•	•	•	•
CP-200 + SSX1	183	176	24	14.1	17.4	1.00	254 X 176 X 178	•	•	6.7	V	55	•	•	•	•	•	•	•	•	•	•
CP-200 + 2 SSX1's	193	185	24	14.1	17.4	1.00	254 X 176 X 178	•	•	7.1	V	55	•	•	•	•	•	•	•	•	•	•
Specifications											Temperature Controllers						Power Supplies					

CE Marked
RoHS Compliant


*Requires bipolar (heat/cool) controller.

Visit <https://tetech.com/product-category/liquid-coolers/> to view our liquid cooler products & data sheets.

TE TECHNOLOGY, INC.  Expert Engineering, Precision Manufacturing
Quality Thermal Solutions Delivered

www.tetech.com • cool@tetech.com • 231-929-3966 • 1590 Keane Drive • Traverse City, MI 49696

Liquid Cooler Performance in a 25 °C Ambient Environment



How to use the Performance Graph:

1. Select Performance Line.

The diagonal lines shown represent cooling performance at the indicated ambient air temperature. Performance lines at other ambient temperatures can be seen on the data sheet for each specific cooler.

2. Select Desired Temperature.

Draw a horizontal line on the graph corresponding to your desired enclosure temperature until it intersects with the performance line corresponding to the ambient temperature at which the cooler is to operate.

NOTE: heating performance is not shown. Contact TE Technology, Inc. if you require this information.

3. Determine Cooling Capacity.

The maximum amount of heat that the cooler can remove is determined by the intersection point (determined in the previous step).

If the heat load exceeds the cooling capacity, then the cooler will not be able to maintain the desired temperature. If the heat load is less, then the cooler can operate with less input power.

TE TECHNOLOGY, INC. [®] Expert Engineering, Precision Manufacturing
Quality Thermal Solutions Delivered

www.tetech.com • cool@tetech.com • 231-929-3966 • 1590 Keane Drive • Traverse City, MI 49696


Temperature Controllers																						
	Maximum Input Voltage (V)	Maximum Output Current (Thermoelectric/Peltier)	PWM Output Frequency (Hz)	PWM Output	Temperature Resolution	Output Power Resolution	Signal Level/Analog Output	Cool or Heat Control Only	Bipolar Cool and Heat Control	Communication	Ramp/Soak Capability	Optional Second Thermistor Input (for Alarm/Data)	Number of Alarm Signals	Maximum Alarm Current	Over current Protection	Fan Speed Control	Display & Keyboard (Integrated)	Display & Keyboard (Optional)	Thermistor Compatibility	Software Source Code Available	Energy-Saving Control Mode for Air Coolers	Product Marking
TC-24-10	26	10	1000	•	0.1	50 steps		•											15K			
TC-36-25 RS485	36	25	2700	•	0.01 °C	512 steps			•	RS485		•	3	25 mA	•			•	5K, 10K, 15K, 50K, 230K	•		
TC-36-25 RS232	36	25	2700	•	0.01 °C	512 steps			•	RS232		•	3	25 mA	•			•	5K, 10K, 15K, 50K, 230K	•		
TC-36-25 RS232-UL	36	25	2700	•	0.01 °C	512 steps			•	RS232		•	3	25 mA	•			•	5K, 10K, 15K, 50K, 230K	•		CE Marked; MET-Labs Listed
TC-48-20 OEM	50	20	337	•	0.1 °C	512 steps	0 - 5 VDC	•		RS232		•	2	1 A					10K, 15K	•		
TC-48-20	50	20	337	•	0.1 °C	512 steps	0 - 5 VDC	•		RS232		•	2	1 A				•	10K, 15K	•		
TC-720 OEM	36	20	337	•	0.01 °C	512 steps	0 - 10 VDC		•	USB	•	•	2	2 A	•	•			5K, 10K-1, 10K-2, 15K, 50K, 230K, user	•	•	
TC-720	36	20	337	•	0.01 °C	512 steps	0 - 10 VDC		•	USB	•	•	2	2 A	•	•	•		5K, 10K-1, 10K-2, 15K, 50K, 230K, user	•	•	

Control Range for Thermistors	
5K	-60 °C to 70 °C *
10K	-20 °C to 85 °C
15K	-20 °C to 100 °C
50K	0 °C to 150 °C
230K	25 °C to 199 °C

RoHS Compliant

* Control range is -40 °C to +199 °C on TC-720 controllers with firmware revision J or older.

Visit <https://tetech.com/product-category/temperature-controllers/> to view our air cooler products & data sheets.

TE TECHNOLOGY, INC.  Expert Engineering, Precision Manufacturing
Quality Thermal Solutions Delivered

www.tetech.com • cool@tetech.com • 231-929-3966 • 1590 Keane Drive • Traverse City, MI 49696